

Han GigaBit Cat8, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 008 3034
Specification	Han GigaBit Cat8, male
HARTING eCatalogue	https://b2b.harting.com/09140083034

Identification

Category	Inserts
Specification	Han [®] Gigabit insert
Features	Suitable for PoE++

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	8
further contacts	+ shielding
Details	Please order crimp contacts separately. Please order adapter module separately.

Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm ²
Rated current	5 A
Rated voltage	50 V
Rated voltage	50 V AC 60 V DC
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Transmission characteristics	Cat. 7 _A Class F _A up to 1,000 MHz Cat. 8 Class II up to 2000 MHz



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
	25 Gbit/s
	40 Gbit/s
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440218 Module for industrial connectors (data)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140083034](#)